



Congratulations on owning the best concentrates device.

Before you start using this product, please read this user manual carefully so that its performances can be made best use of and this unit be used in accordance with the requirements herein.

Please keep this properly for future reference.

1

Product Components



Atomizer

Ring

Tool

2

MIG VAPOR
BRAIN FOGGER

8 52664 38469 3

18+ CE FC Recycle

www.migvapor.com

Product Introduction


Significant Advantages of SUB-OHM CONCENTRATES TANK

- 1.Fits for wax.
- 2.Porous ceramic dual coils, twice-heating atomizing system (Patented).
- 3.Splash-proof inner atomization, more clean and no wax wasted.
- 4.0.5-0.6ohm Highest Surgical Grade 316L stainless steel wire, supporting TC Mod.
- 5.Self-cleaning design.
- 6.Providing the most pure taste and vaping experience.
- 7.Stainless steel base, and 4 air holes.
- 8.For battery and different Box Mod vapor not more than 20 Watts
- 9.Providing the most pure taste and vaping experience.

3

Structure of "Tank"

Concentrates Tank
The Concentrates Tank is an removable structure consisting of stainless steel materials, handmade glass mouthpiece, porous ceramic dual coils.



4

Use Methods of Product

How to use SUB-OHM CONCENTRATES Tank?

1. Use for WAX or CONCENTRATES.
2. Please put wax in the ceramic cup when use the wax vaping.
3. Recommend 10W, not more than 20W or not beyond 300 degrees Fahrenheit.
4. Use ego series battery or control or without control temp Box Mod E-cigarette.

Cautions

Product Use Safety Information

1. Not more than 20W.
2. Not beyond 300F degrees on TC mode.
3. Do not heat the coils for long time without wax inside to avoid damage.

5

4. Dry burn it not too long when clean up.
5. Clean ceramic bowl with a Question tip and alcohol and allow to dry before use.
6. Use a cotton swab or dry cloth to wipe residual material.

Forbidden Users

Forbidden Users:
Minors under the age of 18.
People allergic to concentrates or any components of inhalants.
Pregnant and breast feeding women.

6



folding